
## TOP Wavelengths DFB: 5184 nm & 5263 nm

nanoplus Distributed Feedback Lasers **(DFB)** are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy **(TDLAS)**. Our devices operate **reliably** in more than 50,000 installations worldwide. For more than 20 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

### **Key features:**

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 μm.** 

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of **> 35 dB**, giving your system a low signal to noise ratio against crossinterference.

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.


#### Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver the laser that fits your application."

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**  TO66 with TEC and NTC, sealed with cap and AR coated window



Nanosystems and Technologies GmbH

nanoplus

TOP WAVELENGTH

760.8 nm

5184 & 5285 m
4524 & 4534 nm 5184 & 5263 n
3345 & 3375 nm
2330 & 2334 nm 3240 & 3270 nm
2004.0 nm
1854 & 1877 nm
1742.0 nm
 1651 & 1654 nm
 1560 - 1590 nm
 1512.2 nm
 1392.0 nm
 1278.8 nm



FERED COLL




Nanosystems and Technologies GmbH Nanoplus


# Superior Specifications: 5184 nm & 5263 nm



This data sheet reports performance data of a **sample nanoplus DFB laser at 5263 nm with enhanced specifications.** They are equally valid for 5184 nm.

Standard specifications are available at: <u>https://nanoplus.com/products/distributed-feedback-laser/4600nm-5300nm</u>. These lasers are particularly suitable for nitric oxide (NO) detection.





Typical room temperature cw spectrum of a nanoplus DFB ICL at 5263 nm



electro-optical characteristics	symbol	unit	min.	typical	max.
operating wavelength (at $T_{_{\mathrm{op}}},I_{_{\mathrm{op}}})$	$\lambda_{_{op}}$	nm		5263	
optical output power (at $\lambda_{_{op}}$ )	P <sub>op</sub>	mW		6	
operating current	l <sub>op</sub>	mA		120	
operating voltage	V <sub>op</sub>	V		5	
threshold current	l <sub>th</sub>	mA	25	35	55
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C <sub>i</sub>	nm / mA		0.14	
temperature tuning coefficient	CT	nm / K		0.48	
operating chip temperature	T <sub>op</sub>	°C	+15	+20	+40
operating case temperature*	T <sub>c</sub>	°C	-20	+25	+55
storage temperature*	Ts	°C	-30	+20	+70

\* non-condensing

## laser packaging options

TO66 with TEC and NTC, black cap, AR coated window

Other packaging options may be discussed on request.

Technical drawings & accessories are available at: https://nanoplus.com/products/packaging-options

Please contact <u>sales@nanoplus.com</u> for customized specifications, quotes and further questions. Visit our website for technical notes, application samples or literature referrals.