

Schematic DFB

with spectrum

DFB Quantum Cascade Lasers


(pulsed QCL): 6000 nm - 14000 nm

nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For 25 years nanoplus has set the standard for DFB laser technology and is the only manufacturer

routinely providing DFB lasers at **any wavelength.**

Key features:

- MONOMODE
- PULSED
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 \mum.**

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of **> 35 dB**, giving your system a low signal to noise ratio against crossinterference.

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver a laser that fits your application."

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customerspecific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging.

Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.



High-Heatload (HHL) mount

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**



WAVELENGTH

760-830 nm

830-920 nm

920-1100 nm

1100-1300 nm

1300-1650 nm

1650-1850 nm

1850-2200 nm

2200-2600 nm

2600-2900 nm

2800-4000 nm

4000-4600 nm

4600-5300 nm

5300-5800 nm

5800-6500 nm

6000-14000 nm











Typical Specifications: 6000 nm - 14000 nm (pulsed)

This data sheet reports performance data of a sample DFB QCL at 9800 nm in pulsed operation, which is representative for the entire wavelength range.





Typical room temperature spectrum of a pulsed nanoplus DFB QCL at 9800 nm

Typical mode hop free tuning of a pulsed nanoplus DFB QCL at 9800 nm by current and temperature

electro-optical characteristics (pulsed operation)	symbol	unit	min.	typ	max.
operating wavelength (at $T_{op'}$ I_{op})	$\lambda_{_{op}}$	nm		Please specify to 0.1 nm.	
optical average output power (at λ_{op})	P_{avg}	mW		10	
optical peak output power (at λ_{op})	P_{peak}	mW		200	
operating current	l _{op}	mA		2000	5000
operating voltage	V_{op}	V		15	20
threshold current	l _{th}	mA		1500	
repetition frequency	f	kHz		500	
pulse length	τ	ns		100	
duty cycle	d.c.	%		5	
side mode suppression ratio	SMSR	dB		> 30	
current tuning coefficient	C _I	nm / mA	0		0.15
temperature tuning coefficient	C_{\scriptscriptstyleT}	nm / K		0.7	
operating chip temperature	T_{op}	°C	-10	20	45
operating case temperature*	T _c	°C	10	20	30
storage temperature	T_s	°C	0	20	50

laser packaging options

* non-condensing

High-Heatload Mount (HHL)

Other packaging options may be discussed on request.

Technical drawings & accessories will be soon available at: https://nanoplus.com/products/packaging-options

Please contact sales@nanoplus.com for customized specifications, quotes and further questions.

Visit our website for technical notes, application samples or literature referrals.