

TOP Wavelengths


DFB: 4524 nm & 4534 nm


nanoplus Distributed Feedback Lasers (DFB) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (TDLAS). Our devices operate reliably in more than 50,000 installations worldwide. For more than 20 years nanoplus has set the standard for DFB laser technology and is the only manufacturer

routinely providing DFB lasers at any wavelength.

Key features:

- **MONOMODE**
- **CONTINUOUS WAVE**
- **ROOM TEMPERATURE**
- MODE HOP FREE TUNING





Overgrowth-free DFB device processing

Any custom wavelength is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength between 760 nm and 14 µm.

Our excellent spectral purity is characterized by a large side mode suppression ratio (SMSR) of > 35 dB, giving your system a low signal to noise ratio against crossinterference.

A narrow linewidth below 3 MHz guarantees ultra-precise scanning of the absorption line feature. The high output power of several mW yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver the laser that fits your application."

TO66 with TEC and NTC,

sealed with cap and AR

coated window

We offer various packaging options, e.g. several free space housings including TEC and NTC, fiber coupling, collimation and custom designs. What do you require?

If you require custom specifications, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a fully vertically integrated company, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in Germany. To quarantee consistent product quality we apply a strict and ISO certified quality management system at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: We make market leaders!









WAVELENGTH

760.8 nm

1278.8 nm

1392.0 nm

1512.2 nm

1742.0 nm

2004.0 nm

1560 - 1590 nm

1651 & 1654 nm

1854 & 1877 nm


2330 & 2334 nm

3240 & 3270 nm

3345 & 3375 nm

4524 & 4534 nm

5184 & 5263 nm



Superior Specifications: 4524 nm & 4534 nm




Nanosystems and




This data sheet reports performance data of a **sample nanoplus DFB laser at 4524 nm with enhanced specifications.** They are equally valid for 4534 nm.

Standard specifications are available at: https://nanoplus.com/products/distributed-feedback-laser/4000nm-4600nm.

These lasers are particularly suitable for nitrous oxide (N₂O) detection.





Typical room temperature cw spectrum of a nanoplus DFB ICL at 4524 nm

Typical mode hop free tuning of a nanoplus DFB ICL at 4524 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typical	max.
operating wavelength (at T _{op} , I _{op})	$\lambda_{\sf op}$	nm		4524	
optical output power (at λ_{op})	P_{op}	mW		8	
operating current	l _{op}	mA		120	
operating voltage	V_{op}	V		5	
threshold current	I _{th}	mA	20	30	40
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	$C_{_{_{\rm I}}}$	nm / mA		0.12	
temperature tuning coefficient	C_{T}	nm / K		0.45	
operating chip temperature	T_{op}	°C	+15	+20	+40
operating case temperature*	T _c	°C	-20	+25	+55
storage temperature*	T _s	°C	-30	+20	+70

* non-condensing

laser packaging options

TO66 with TEC and NTC, black cap, AR coated window

Other packaging options may be discussed on request.

Technical drawings & accessories are available at: https://nanoplus.com/products/packaging-options

Please contact <u>sales@nanoplus.com</u> for customized specifications, quotes and further questions. Visit our website for technical notes, application samples or literature referrals.