

Schematic DFB

with spectrum

TOP Wavelengths

DFB: 1651 nm & 1654 nm

nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For more than 20 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING

Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 \mum.**

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of > **35 dB**, giving your system a low signal to noise ratio against crossinterference.

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver the laser that fits your application."

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require custom specifications, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a fully vertically integrated company, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in Germany. To guarantee consistent product quality we apply a strict and ISO certified quality management system at all levels.



nanoplus DFB lasers on TO66, TO5, TO5.6, c-mount and SM-BTF

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**

TOP WAVELENGTH

760.8 nm

1278.8 nm

1392.0 nm

1512.2 nm

1560 - 1590 nm

1651 & 1654 nm

1742.0 nm

1854 & 1877 nm

2004.0 nm

2330 & 2334 nm

3240 & 3270 nm

3345 & 3375 nm

4524 & 4534 nm

5184 & 5263 nm









Superior Specifications: 1651 nm & 1654 nm







This data sheet reports performance data of a sample nanoplus DFB laser at 1651 nm with enhanced specifications.

They are equally valid for 1654 nm. Standard specifications are available at:

https://nanoplus.com/products/distributed-feedback-laser/1650nm-1850nm.

These lasers are particularly suitable for methane (CH₄) detection.





Typical room temperature cw spectrum of a nanoplus DFB laser at 1651 nm

Typical mode hop free tuning of a nanoplus DFB laser at 1651 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typical	max.
operating wavelength (at T _{op} , I _{op})	$\lambda_{\sf op}$	nm		1651	
optical output power (at λ_{op})	P_{op}	mW		8	
operating current	l _{op}	mA		70	
operating voltage	V_{op}	V		2	
threshold current	l _{th}	mA	10	20	30
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C	nm / mA	0.008	0.012	0.015
temperature tuning coefficient	C_{T}	nm / K	0.10	0.11	0.14
operating chip temperature	T_{op}	°C	+20	+25	+45
operating case temperature*	T_{c}	°C	-20	+25	+55
storage temperature*	T_{S}	°C	-40	+20	+80

laser packaging options

* non-condensing

TO5 with TEC and NTC, black cap, AR coated window

TO56 without TEC or NTC, sealed, window

c-mount without TEC or NTC

butterfly package with TEC and NTC, SM or PM fiber, FC/APC connector

chip on carrier without TEC, with NTC

Technical drawings & accessories are available at: https://nanoplus.com/products/packaging-options

Please contact sales@nanoplus.com for customized specifications, quotes and further questions.

Visit our website for technical notes, application samples or literature referrals.

nanoplus Nanosystems and Technologies GmbH, www.nanoplus.com, phone: +49 (0) 3693 50 5000-0, email: sales@nanoplus.com

copyright nanoplus Nanosystems and Technologies GmbH 2023, all rights reserved. Technical data is subject to change without notice.