

Schematic DFB

with spectrum

## **TOP Wavelengths**

DFB: 2004.0 nm

nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For more than 20 years nanoplus has set the standard for DFB laser technology and is the only manufacturer


routinely providing DFB lasers at any wavelength.

## nm

MONOMODE

**Key features:** 

- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 \mum**.

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of > **35 dB**, giving your system a low signal to noise ratio against crossinterference.

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver the laser that fits your application."

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.



nanoplus DFB lasers on TO66, TO5, TO5.6, c-mount and SM-BTF

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!** 

TOP WAVELENGTH

760.8 nm

1278.8 nm

1392.0 nm

1512.2 nm

1560 - 1590 nm

1651 & 1654 nm

1742.0 nm

1854 & 1877 nm

2004.0 nm

2330 & 2334 nm

3240 & 3270 nm

3345 & 3375 nm

4524 & 4534 nm

5184 & 5263 nm













## **Superior Specifications:** 2004.0 nm



This data sheet reports performance data of a sample nanoplus DFB laser at 2004.0 nm with enhanced specifications. Standard specifications are available at: https://nanoplus.com/products/distributed-feedback-laser/1850nm-2200nm. These lasers are particularly suitable for carbon dioxide (CO<sub>2</sub>) detection.





Typical room temperature cw spectrum of a nanoplus DFB laser at 2004.0 nm

Typical mode hop free tuning of a nanoplus DFB laser at 2004.0 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typical	max.
operating wavelength (at $T_{op'}$ $I_{op}$ )	$\lambda_{\sf op}$	nm		2004.0	
optical output power (at $\lambda_{op}$ )	$P_{op}$	mW		5	
operating current	l <sub>op</sub>	mA		100	
operating voltage	$V_{op}$	V		2	
threshold current	l <sub>th</sub>	mA	5	10	25
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	$C_l$	nm / mA	0.019	0.025	0.035
temperature tuning coefficient	$C_{T}$	nm / K	0.18	0.19	0.21
operating chip temperature	$T_{op}$	°C	+20	+30	+45
operating case temperature*	$T_{c}$	°C	-20	+25	+55
storage temperature*	$T_s$	°C	-40	+20	+80

## laser packaging options

\* non-condensing

TO5 with TEC and NTC, black cap, AR coated window

TO56 without TEC or NTC, sealed, window

c-mount without TEC or NTC

butterfly package with TEC and NTC, SM or PM fiber, FC/APC connector

chip on carrier without TEC, with NTC

Technical drawings & accessories are available at: https://nanoplus.com/products/packaging-options

Please contact <a href="mailto:sales@nanoplus.com">sales@nanoplus.com</a> for customized specifications, quotes and further questions.

Visit our website for technical notes, application samples or literature referrals.

nanoplus Nanosystems and Technologies GmbH, www.nanoplus.com, phone: +49 (0) 3693 50 5000-0, email: sales@nanoplus.com

copyright nanoplus Nanosystems and Technologies GmbH 2023, all rights reserved. Technical data is subject to change without notice.